

RapidPak RP-25

Pure & Simple... *The Best Solution for Medical Packaging!*



Exceptionally High Cycle Rates Through the Use of Servo Motor Technology

- Greater precision of motion, and eliminates compressed air
- Servo-driven plug assist optimizes forming, and allows for down-gauging of film thickness

Allen Bradley CompactLogix System and Modem


- Allen Bradley PanelView Plus Touchscreen
- Faster, easier maintenance
- 24/7 modem service

Mechanical Simplicity; Fewer Moving Parts


- Reduces downtime, easier maintenance, and lower parts costs
- Reduces the need for trained expert personnel

Readily Available Parts and Components

- Industry standard off-the-shelf components
- Online parts ordering, at www.rapidpak.com



RapidPak RP-25



Servo Motor Precision


- Servo motors on all major machine functions. Continual feedback allows Servos to move faster, smoother, and more accurate in pneumatic systems.



- Separate pre-heat is more hygienic, maximizes heating and forming times, and allows faster cycle rates.
- Machine mounted electrical panel and NEMA 4 water-tight components ensure reliable start-up after aggressive cleaning
- Easily sourced parts; lower annual cost.
- Cutting Systems: IMD: Rotary Knives
XMD: Guillotine Knives
- Options Available: Discharge conveyor
Confirmation station
Top registration
Tower-mounted film labeler
- Guards remain on machine – eliminates handling; easy-open access
- Custom frame welded and machined to $\pm 0.001''$ tolerance ensures consistent, long-term performance and reduces parts wear.



Allen Bradley Parallel Plus Touchscreen



Servo-Driven Die Closing Lift System

SPECIFICATIONS:


- Up to 127 mm (5") max. formed pocket.
- Std. Web Widths: 285 mm (11.22")
320 mm (12.59")
420 mm (16.54")
430 mm (16.93")
- Std. Index Lengths: 200 mm (7.87")
240 mm (9.45")
300 mm (11.80")
340 mm (13.38")
400 mm (15.75")
- Std. open loading area: Up to 2.13 m (7'-0")



Convenient Parts Sourcing



Sanitary Tilt-Away Guards




Plug Assist



Sanitary Tubular Frame

UTILITIES

- Electrical: 230/3/60. Amperage to be determined once machine is configured.
- Compressed Air: Typically 2-3 cfm, 80-90 psi
- Water: 30-50 gallons per hour at 10-50 psi



Hermetically Sealed Weldments